



6-641337-3 | MP-66U-F-1  
**Modular Plug, 6P/6C, Unshielded, Flat Oval, 100 pcs**

## Body Features

Conductor Type	Solid   Stranded
----------------	------------------

## Configuration Features

Number of Positions	6
Keyed	No

## Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm
Number of Contacts Loaded	6

## Dimensions

Cable Jacket Outside Diameter Range	0.09–0.26 in   2.29–6.61 mm
Conductor Outside Diameter	0.034–0.039 in   0.86–0.99 mm
Conductor Wire Size	26–24 AWG

## Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

## Packaging Features

Packaging Quantity	100
--------------------	-----

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Cable Type	Flat oval, unshielded
Performance Category	Category 3
Connector Style	Plug
Jack Type	RJ11
Latch Style	Standard

6-641337-3 | MP-66UF-1

Product Type	Connector
Shielded	No

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------