

## 2-Port DisplayPort 1.2 KVM Switch w/Audio, Cables and USB Peripheral Sharing

MODEL NUMBER: **B004-DP2UA2-K**



### Description

The desktop B004-DP2UA2-K 2-Port DisplayPort 1.2 KVM Switch lets you access, control, boot and reboot two 4K-enabled DisplayPort 1.2 computers using one DisplayPort monitor, keyboard and mouse. Switching between computers is quick and simple using a connected remote port selector, keyboard hotkeys or mouse scroll wheel. The B004-DP2UA2-K supports Multi-Stream Transport (MST), so you can use multiple monitors via one DisplayPort connector.

By adding a powered USB 2.0 hub (sold separately) to the switch, you increase functionality by allowing USB peripherals—such as printers, hard drives, scanners, webcams and thumb drives—to be shared between computers. You can also plug microphones and speakers into the 3.5 mm mini-stereo jacks. Because audio and the B004-DP2UA2-K can be switched independently of each other, you can access one computer while listening to audio on the other.

All necessary cables are included. The B004-DP2UA2-K supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K), 2.1-channel surround sound, HD Audio and HDCP. All connected computers receive the console monitor's EDID information to ensure top video quality and prevent any delay or change in video resolution when switching computers.

The B004-DP2UA2-K is easy to set up with no software or drivers to install. It supports Windows, Mac, Linux and Sun. It also supports DisplayPort Dual Mode (DP++) for directly outputting single-link DVI or HDMI signals via adapter.

### Features

#### Access and Control Two 4K-Enabled DisplayPort 1.2 Computers with One KVM Switch

- Switch between computers using remote port selector, hotkeys or mouse wheel
- Supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K)

### Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K)
- Switch between computers via remote selector, hotkeys or mouse
- Supports DisplayPort Dual Mode (DP++)
- Includes necessary DisplayPort, USB and audio cables
- Compatible with Windows®, Mac®, Linux and Sun

### System Requirements

#### Console

- DisplayPort monitor capable of supporting highest resolution of any computer in installation
- USB keyboard/mouse
- Speakers with 3.5 mm male connector (if using audio function)

#### Computer

- DisplayPort audio/video port
- USB port
- 3.5 mm audio jack (if using audio function)

MST requires source computers to be compatible with DisplayPort 1.2 and either a Tripp Lite DisplayPort hub or DisplayPort monitors with the ability to daisy-chain

### Package Includes

- B004-DP2UA2-K 2-Port DisplayPort 1.2 KVM Switch
- (2) DisplayPort monitor cables
- (2) USB A/B device cables
- (2) 3.5 mm stereo audio cables
- Remote port selector
- Owner's manual

- Supports DisplayPort Dual Mode (DP++) for directly outputting single-link DVI or HDMI signals via adapter
- All connected computers receive EDID information to ensure top video quality without delay
- Auto Scan feature cycles between computers at regular intervals for at-a-glance observation of activity
- Multi-Stream Transport (MST) lets you use multiple monitors via one DisplayPort connector

#### Independent Audio Switching

- 3.5 mm mini-stereo speaker and microphone jacks allow sharing of audio equipment between computers
- Listen to audio files on one computer while accessing the other computer
- Supports 2.1-channel surround sound and HD Audio (through DisplayPort playback)

#### Independent USB 2.0 Peripheral Sharing

- Adding an optional USB hub (sold separately) allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

#### Compatible with Major Operating Systems

- Compatible with Windows, Mac, Linux and Sun
- Easy to set up with no software or drivers to install
- Bus-powered, so no external power supply required
- Includes necessary DisplayPort, USB and audio cables
- HDCP-compliant
- Works with multimedia keyboards, multi-function mice, and wireless keyboards and mice

## Specifications

OVERVIEW	
Users	1
PHYSICAL	
Unit Dimensions (hwd / in.)	1.1 x 3.7 x 3.7
Unit Dimensions (hwd / cm)	2.68 x 9.30 x 9.37
Unit Weight (lbs.)	0.26
Unit Weight (kg)	0.12
Housing Color	Black
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	USB; DisplayPort
SPECIAL FEATURES	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cat5 KVM Switch	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>