

## Replacement Battery Cartridge for Select 72V Tripp Lite SmartOnline® UPS Systems

MODEL NUMBER: **RBC72S**



### Highlights

- Replacement internal battery for select Tripp Lite UPS systems
- Rugged leakproof construction
- No maintenance required
- Wide range of operating temperatures
- Preassembled and prewired for immediate installations

### Package Includes

- RBC72S Replacement 72V Battery Cartridge

### Description

The Tripp Lite RBC72S Replacement Battery Cartridge breathes new life into select Tripp Lite UPS systems whose internal batteries are expired or not working. Built to function in a wide range of operating temperatures, the RBC72S has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. The leakproof, no-maintenance RBC72S comes preassembled and prewired for quick and easy installation in your UPS system. Reusable packaging holds expired batteries for delivery to the nearest recycling center. Compatible with Tripp Lite's [SU3000RTXLCD2U](#), [SU3000LCD2UHV](#), [SUINT3000LCD2U](#) and other models recommending its use.

### Features

#### Replacement Internal Battery for Select Tripp Lite UPS Systems

- Screened and certified to restore UPS system's runtime performance to original specs
- Compatible with Tripp Lite's [SU3000RTXLCD2U](#), [SU3000LCD2UHV](#), [SUINT3000LCD2U](#) and other models recommending its use
- Preassembled and prewired for immediate installation
- Designed for a wide range of operating temperatures
- Rugged leakproof construction
- No maintenance required
- Reusable packaging for delivering expired batteries to recycling center

## Specifications

BATTERY	
DC System Voltage (VDC)	72
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / in.)	3.78 x 9.06 x 19.3
Shipping Dimensions (hwd / cm)	9.60 x 23.01 x 49.02
Shipping Weight (lbs.)	40.12
Shipping Weight (kg)	18.21
Unit Dimensions (hwd / in.)	2.66 x 8.34 x 17.91
Unit Dimensions (hwd / cm)	6.76 x 21.18 x 45.49
Unit Weight (lbs.)	37.26
Unit Weight (kg)	16.8
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
Operating Elevation (ft.)	10,000 ft.
Storage Elevation (ft.)	10,000 ft.
Operating Elevation (m)	3,000 m
Storage Elevation (m)	3000 m
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>