

## SmartRack 21U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRW21U**



### Description

The SRW21U SmartRack 21U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 pounds.

The side panels and front door lock securely to help prevent damage, tampering or theft. The front, top, bottom and removable side panels are vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing.

The SRW21U comes fully assembled and ready to mount to the wall, or use Tripp Lite's optional [SRCASTER](#) rolling caster kit to make it a mobile rack. Square and threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 16.5 inches deep, such as network switches and patch panels.

### Features

#### Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 21U of space
- Maximum load capacity of 200 lb.

#### Keeps Important Equipment Secure

- Side panels and front door lock securely to help prevent damage, tampering or theft
- Vented panels allow generous airflow that keeps equipment cool
- Rotate cabinet 180° before mounting to open reversible front door left or right

### Highlights

- Maximum load capacity of 200 lb.
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Secures 21U of 19 in. rack equipment up to 16.5 in. deep
- Mounts to wall or rolls on floor (with optional [SRCASTER](#))

### Package Includes

- SRW21U SmartRack 21U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (44) M6 screws
- (44) M6 cage nuts
- (44) M6 cup washers
- (44) 12-24 screws
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual



- Convenient ports with removable covers allow cable routing through top and bottom

#### Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Mounts to wall or rolls on floor with Tripp Lite's optional [SRCASTER](#) caster kit
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 16.5 in. deep, such as network switches and patch panels
- Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in
- Rails support square-hole or threaded-hole mounting
- Rack spaces numbered for easy reference

#### Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS(Payment Card Industry Data Security Standard) compliance

## Specifications

PHYSICAL	
Rack Height (U Spaces)	21
Maximum Device Depth (in.)	16.5
Maximum Device Depth (cm)	41.9
Minimum Device Depth (in.)	3
Minimum Device Depth (cm)	7.62
Shipping Dimensions (hwd / in.)	45.87 x 26.61 x 18.98
Shipping Dimensions (hwd / cm)	116.51 x 67.59 x 48.21
Shipping Weight (lbs.)	67.80
Shipping Weight (kg)	30.75
Unit Dimensions (hwd / in.)	40.87 x 23.63 x 17.72
Unit Dimensions (hwd / cm)	103.81 x 60.02 x 45.01
Unit Weight (lbs.)	51.00
Unit Weight (kg)	23.13
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

CERTIFICATIONS	
Certifications	UL/CSA 60950-1, EIA-310-E
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>