

## SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRWF6U**



### Description

The SRWF6U SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 pounds.

Because the low-profile cabinet mounts vertically, it extends less than 12 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels. In addition to 6U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF6U comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

### Features

#### Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 6U of space
- Low-profile vertical-mount cabinet extends less than 12 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels
- Also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep
- Maximum load capacity of 150 lb.

### Highlights

- Maximum load capacity of 150 lb.
- Locking steel cabinet vented to keep equipment cool
- Secures 6U of 19 in. rack equipment up to 20 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

### Package Includes

- SRWF6U SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

#### Keeps Important Equipment Secure

- Top panel and reversible front door lock securely to help prevent damage, tampering or theft
- Front door latch also accommodates a user-supplied padlock for added security
- Vented cabinet keeps equipment cool
- Convenient ports with removable covers allow cable routing through top and bottom

#### Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in
- Threaded mounting holes support M6 or 12-24 mounting
- Rack spaces marked for easy reference

#### Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

## Specifications

PHYSICAL	
Rack Height (U Spaces)	6
Maximum Device Depth (in.)	20
Maximum Device Depth (cm)	50.80
Minimum Device Depth (in.)	17
Minimum Device Depth (cm)	43.18
Shipping Dimensions (hwd / in.)	34.25 x 31.1 x 16.93
Shipping Dimensions (hwd / cm)	87 x 78.99 x 43
Shipping Weight (lbs.)	70.5
Shipping Weight (kg)	31.98
Unit Dimensions (hwd / in.)	28.8 x 25.6 x 11.5
Unit Dimensions (hwd / cm)	73.15 x 65.02 x 29.21
Unit Weight (lbs.)	64
Unit Weight (kg)	29.03
Color	Black
Weight Capacity - Stationary (lbs.)	150
Weight Capacity - Stationary (kg)	68.0
CERTIFICATIONS	
Certifications	EIA-310-E



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>