

USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft.

MODEL NUMBER: **U324-003-KJ**



Highlights

- Connects two USB-A devices, such as computers and flash drives
- Data transfer rates up to 5 Gbps
- Data flows both directions simultaneously
- Twisted 28/24 data/power lines
- Backward compatible with earlier USB generations

Package Includes

- U324-003-KJ USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft.

Description

The Tripp Lite U324-003-KJ USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable allows you to terminate a USB connection in a universal keystone wallplate, outlet box or panel. Ideal for giving your conference room a professional, clutter-free look, this cable can complete an in-wall run and keep components out of sight in a closet or another room to eliminate cable clutter.

The U324-003-KJ connects two USB-A devices, such as computers, keyboards, external hard drives and flash drives. It supports data transfer rates up to 5 Gbps—ten times the speed of USB 2.0—as well as more efficient power. The bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by ten times.

Backward compatible with earlier USB generations, the three-foot U324-003-KJ features premium foil and braid shielding to deliver reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated copper contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Mount a USB 3.0 Type-A Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate, outlet box or panel
- Gives your conference room a professional, clutter-free look
- Connects computers, keyboards, external hard drives, flash drives and other USB-A devices
- Data transfer rates up to 5 Gbps
- Bi-directional data interface allows data to flow both directions
- Backward compatible with earlier USB generations

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated copper contacts
- Integral strain relief for long life



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Black; Blue
CONNECTIONS	
Side A - Connector 1	(1) USB 3.0 A (MALE)
Side B - Connector 1	(1) USB 3.0 A (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>