

USB 3.0 SuperSpeed to VGA Adapter, 512MB SDRAM - 2048x1152,1080p

MODEL NUMBER: U344-001-VGA



Description

Tripp Lite's U344-001-VGA USB 3.0 to VGA Multi Monitor External Video Adapter allows you to connect an additional monitor or projector to a computer/laptop's USB 3.0 port. Up to six adapters can be used simultaneously, allowing the user to connect up to six additional monitors to a single computer. Once the installation is done, the computer screen appears on the add-on monitor(s) without the hassle of function keys to swap to a second monitor. Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz). Windows and Intel Mac compatible.

Features

- Add an additional VGA monitor through a single USB 3.0 port
- Use up to six adapters simultaneously, adding up to six additional monitors to a single computer
- View large spreadsheets across multiple screens by extending video amongst all monitors
- Play video on one monitor while working on another
- Do multiple screen presentations from a laptop computer
- Bus powered...no external power adapter needed
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8.5 and later. Supports both 32- and 64-bit.
- Uses DisplayLink DL3100 chipset

Specifications

ENVIRONMENTAL

Highlights

- Add an additional VGA monitor through a single USB 3.0 port
- Up to six adapters can be added to one computer
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Windows and Intel Mac compatible
- Compatible with Ubuntu 14.04.2

System Requirements

- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8.5 and later. Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- (1) U344-001-VGA USB 3.0 to VGA Adapter
- (1) Driver CD
- (1) Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	50 to 104 F (10 to 40 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Relative Humidity	Less than 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	HD15 (FEMALE)
CERTIFICATIONS	
Approvals	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>