

UTILITY STORAGE



Innovative and practical solutions
to haul utility tools and gear
around the jobsite.

**KLEIN
TOOLS®**

UTILITY STORAGE



NEW! Lineman Backpack

Klein's new Lineman's Backpack is a unique new option for transporting tools to the jobsite.



5185ORA

Wide Opening

easily accommodates helmets, belts and other equipment.

Large Front Pocket

for separate storage of gaffs, rubber gloves or other equipment.



Padded back area.

Durable, double stitched plastic bottom with drain holes.

Adjustable padded shoulder straps with adjustable chest strap.



Manufactured in USA of U.S. and imported components.

KLEIN TOOLS®

Nut and Bolt Pouch

- Includes interior pocket.
- Top sides of pouch reinforced with leather to maintain shape.
- Inside bottom is reinforced with leather and ventilating eyelet.
- Metal snaps provided on loops for easy attachment to belts up to 3" (76mm) wide.
- Top edge reinforced with 1/4" (6 mm) rope.



51A

Cat. No.	Pockets	Length	Width	Depth	Weight (lbs)
51A	1 interior	9" (229 mm)	10" (254 mm)	3.5" (9 mm)	1

Hook for Aerial-Baskets

- All weather, durable, nylon 66 polymer.
- Most manufacturers' aerial basket trucks accommodate bucket hook.



5144H

Cat. No.	Weight (lbs.)
5144H	.30

Vinyl Equipment Bags

- Outside pockets with Velcro® fastening.
- Adjustable, padded shoulder strap.
- Durable, double-stitched plastic bottom.
- Two heavy duty, slide-action buckles to conveniently close bag.
- Nylon webbing extends down side of bag from handles and shoulder strap for extra support and durability.
- Wide-opening, steel frame securely riveted to top of bag helps maintain bag's shape.



5181ORA

Cat. No.	Color	Pockets	Length	Height	Width	Weight (lbs)
5181ORA	orange	1 outside	24" (610 mm)	20" (508 mm)	10" (254 mm)	7
5182BLA	black	2 outside	24" (610 mm)	20" (508 mm)	10" (254 mm)	7

Velcro® is a registered trademark of Velcro Industries B.V.

For Professionals... Since 1857®

Utility Storage Solutions



Hard-Body Buckets

NEW! w/ Kickstand



5144BHB



5144BHB140S



5144HBS

- **Kickstand for stability and proper orientation.** (Cat. No. 5144BHB)
- Orange, non-conductive plastic exterior maintains bucket shape. (Cat. Nos. 5144BHB and 5144HBS)
- Molded polypropylene bottom with drain holes.
- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite.
- Includes leather skinning knife sheath (Cat. No. 5144HBS)
- 15 interior pockets and 14 exterior pockets, 29 pockets total. (Cat. No. 5144BHB140S)
- Includes web handles for easier transport. (Cat. No. 5144HBS and Cat. No. 5144BHB140S)
- Cat. No. 5144H hooks sold separately.



5144HBS Knife Sheath

Cat. No.	Description	Color	Pockets	Length	Height	Width	Weight (lbs)
5144BHB	hard body kick stand oval bucket w/14 interior pockets	orange	14	14" (356 mm)	10" (254 mm)	7" (178 mm)	2
5144BHB140S	hard body tote w/29 pockets & handle	black	29	14" (356 mm)	10" (254 mm)	7" (178 mm)	3
5144HBS	hard body oval bucket w/14 interior pockets	orange	14	14" (356 mm)	10" (254 mm)	7" (178 mm)	2

Aerial Aprons with Magnet

- Sewn-in magnet design won't catch on gloves.
- Includes ten hand tool pockets, two pouches, hammer loop and two drill bit holders. (Cat. No. 51829MHS has 1 drill bit holder).
- Large pouch for hot stick and attachments. (Cat. No. 51829MHS)
- Two pouches reinforced with heavy duty rivets.
- Cat. No. 5144 hooks sold separately.



51829M

NEW! Hot Stick Pocket



51829MHS

Cat. No.	Pockets	Height	Width	Weight (lbs)
51829MHS	18 pockets with hot stick pocket and magnet	32" (813 mm)	27.5" (699 mm)	4
51829M	18 pockets and 1 magnet	23" (584 mm)	24" (609 mm)	4
51829	18 pockets	23" (584 mm)	24" (609 mm)	4



Load Rated Canvas Buckets

- High-density polyethylene top ring for strength and chemical resistance.
- Polypropylene-rope handle reinforced with leather for wear resistance and strength.

5104 Series

- **100 lbs Max Load Rating.**
- No. 1 canvas.
- Leather reinforced bottom.
- Inside pocket measures 8" x 8" (203 mm x 203 mm).

**LOAD
RATED**

Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5104	12" (305 mm)	17" (432 mm)	N/A	2.71
5104S	12" (305 mm)	17" (432 mm)	swivel snap (Cat. No. 2012)	2.93

5109 Series

- **75 lbs Max Load Rating.**
- No. 6 canvas.
- Black molded polypropylene bottom with drain holes.

Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5109	12" (305 mm)	15" (381 mm)	N/A	2.06
5109P	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket	2.12
5109S	12" (305 mm)	15" (381 mm)	swivel snap (Cat. No. 2012)	2.35
5109PS	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket and swivel snap (Cat. No. 2012)	2.40



5109

5104

▲WARNING:

- Inspect for damage before each use.
- Remove from service if bucket shows signs of wear.
- Never exceed the working load limit.

Vinyl Bucket Top

- Top cover for canvas bucket designed to keep the elements out and tools securely inside.
- Compatible with Klein Tools 5104 and 5109 series buckets.
- Velcro® closure.
- Includes safety strap loop to ensure connection to bucket.
- Bucket not included.



51TOP

Cat. No.	Diameter	Height	Weight (lbs)
51TOP	12.5" (318 mm)	3.5" (89 mm)	.4

Velcro® is a registered trademark of Velcro Industries B.V.

Mini Leather-Bottom Bucket

- Leather-reinforced bottom.
- Heavy duty natural canvas.
- Rope handle.
- Makes a great gift!



5104MINI

Cat. No.	Diameter	Height	Weight (lbs.)
5104MINI	5" (127 mm)	6" (152 mm)	.4



Manufactured in USA of U.S. and imported components.

Klein Tools, since 1857, proudly manufactures utility storage products like lineman buckets, bags, aprons and pouches at its Fort Smith, Arkansas facility.

**Fort Smith,
Arkansas**
Klein Tools, Inc.

**KLEIN
TOOLS**



www.kleintools.com

© 2013 Klein Tools, Inc.
Printed in U.S.A. 96836 Rev. B