



HOLIS
From Tyco Security Products

Network Video Recorder

4-channel



Features That Make a Difference

- Small footprint and quiet operation
- Fits almost any application and location
- Quick to install and easy to use
- 4 channels of 1080p real-time live view
- H.264/MJPEG dual codec decoding
- HDMI/VGA simultaneous video output
- All channel synchronous real-time playback
- ONVIF-compliant
- Remote network monitoring with web browser
- P2P Capability - Makes setting up remote viewing simple and risk-free
- Mobile apps for IOS and Android
- Supports Plug & Play, 4 PoE ports
- 3 storage options

The Holis 4-channel Network Video Recorder is an affordable solution for any small security application. The NVR is small enough to fit into most locations, but can store 1, 2, or 4 terabytes of data. Holis supports many brands of IP cameras and is ONVIF-compliant. This NVR supports 4 channels of 1080p real-time live views. It is quick to install with automatic discovery and configuration of matching cameras as they are connected. It is also very easy to learn and use for great customer satisfaction.

SPECIFICATIONS

System	
Main Processor	Dual-core embedded processor
Operating System	Embedded LINUX
Video	
IP Camera Input	4 input channels, all with PoE
Display	
Interface	1 HDMI, 1 VGA
Resolution	1920 x 1080, 1280 x 1024, 1280 x 720, 1024 x 768
Display Split	1/4
OSD	Camera title, time, video loss, camera lock, motion detection, recording
Recording	
Compression	H.264, MJPEG
Resolution	1080p, 720p, D1
Record Rate	200/240ips at D1, 100/120ips at 720p, 50/60ips at 1080p
Bit Rate	48~8192kbps
Record Mode	Manual, schedule (regular, continuous, MD), stop
Record Interval	1-120 minutes (default: 60 minutes), pre-record: 1-30 seconds, post record: 10-300 seconds
Video Detection	
Trigger Events	Recording, PTZ, tour, video push, email, FTP, buzzer, screen tips
Video Detection	Motion detection, video loss, camera blank
Playback & Backup	
Sync Playback	1/4
Search Mode	Time/date, motion detection & exact search (accurate to second), smart search

Playback Function	Play, pause, stop, rewind, fast play, slow play, next file, previous file, next camera, previous camera, full screen, repeat, shuffle, backup selection, digital zoom
Backup Mode	USB device, network
Network	
Ethernet	1 RJ-45 port (10/100M)
Network Function	HTTP, TCP/IP, IPv4/IPv6, UPNP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPOE, DDNS, FTP, IP Search
Maximum User Access	128 users
Smart Phone	iPhone, iPad, Android
Storage	
Internal HDD	1 SATA port, up to 4TB
Auxiliary Interface	
USB	2 ports (1 rear), USB2.0
General	
Power Supply	DC48V/1.5A
Power Consumption	NVR: 10W (without HDD); PoE port: max 15W each
Working Environment	0°C - 55°C
Dimensions	205 x 205 x 45mm
Weight	600-700g (without HDD)

Model Number	Model Description
HOLNVR04100	4 Channel NVR, 4 Port PoE, 1TB with Euro Power Cord
HOLNVR04100UK	4 Channel NVR, 4 Port PoE, 1TB with UK Power Cord
HOLNVR04200	4 Channel NVR, 4 Port PoE, 2TB with Euro Power Cord
HOLNVR04200UK	4 Channel NVR, 4 Port PoE, 2TB with UK Power Cord
HOLNVR04400	4 Channel NVR, 4 Port PoE, 4TB with Euro Power Cord
HOLNVR04400UK	4 Channel NVR, 4 Port PoE, 4TB with UK Power Cord

System Connection

