

AXIS Companion Switch 4CH

4-port 10/100 Mbps PoE+ switch

The palm-sized AXIS Companion Switch delivers network and power for up to 4 network cameras with Plug and Play installation. Using AXIS Companion Switch as a central power source, simplifies both installation and maintenance. The switch, together with the AXIS Surveillance microSDXC™ Card 64 GB, are intended for small systems with only a few cameras and basic video storage requirements.

- > **4-port 10/100 Mbps 802.3af/at PoE+**
- > **1-port 10/100 Mbps switch**
- > **60 W PoE power budget**
- > **LED indicators for network diagnostics / PoE Status**
- > **Level VI compliant for energy efficiency**



AXIS Companion Switch 4CH

General	
Supported products	AXIS Companion Line cameras
Casing	Metal Color: White
Environment	Indoor
Dimensions	90 x 80 x 21 mm 3.54 x 3.15 x 0.83 in
Weight	172 g (0.38 lb)
Input power	100–240 V AC, 50–60 Hz Max 62 W Power plug polarity: Center-pin positive
Max. output power	Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3 Power over Ethernet (PoE+) IEEE 802at Type 2 Class 4 Total max 60 W 4x15 W, 2x30 W or 1x30 W + 2x15 W
Connectors	1x RJ45 10BASE-T/100BASE-TX 4x RJ45 10BASE-T/100BASE-TX PoE
Operating conditions	0 °C to 50 °C (32 °F to 122 °F) Humidity 5–95% RH (non-condensing)
Storage conditions	-10 °C to 70 °C (14 °F to 158 °F) Humidity 5–95% RH (non-condensing)
Approvals	EN 55022:2010/55032:2012 + AC : 2013 Class B EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 Subpart B Class B ICES-003 Class B IEC/EN/UL 60950-1 IEC/EN/UL 62368-1 CE WEEE EN 50581
Included accessories	Installation Guide Power cord Power adapter Rubber feet (4x)
Warranty	Axis 3-year warranty, see www.axis.com/warranty

Environmental responsibility:
www.axis.com/environmental-responsibility