

AXIS T91A57 Pole Mount 60-400 mm

A smart mount for poles of any size

AXIS T91A57 Pole Mount is a high-quality pole mount, designed for use with AXIS T91G61 Wall Mount and AXIS T98A Surveillance Cabinet Series. It is adjustable, and fits poles of between 60-400 mm (2.4 in-15.7 in) in diameter. The pole mount has an IK10 rating for impact resistance, which safeguards it against vandalism. It features a closed back and a cable gasket, which means it is also protected against insect infestation.

- > Indoor and outdoor use
- > Impact-resistant to prevent vandalism
- > Cable gasket to prevent insect infestation
- > Robust and safe



AXIS T91A57 Pole Mount 60-400 mm

General		Environment	Indoor Outdoor
Supported products	AXIS T91G61 Wall Mount AXIS T98A Surveillance Cabinet	Approvals	IEC/EN 60950-1 IEC/EN 60950-22 EN 50581 IEC 62262 IK10
Casing	IK10-rated impact resistant aluminum mount Color: White NCS S 1002-B	Included accessories	Installation Guide Insect-proof cable gasket Steel straps
Dimensions	190 x 214 x 67 mm (W x H x L) (7.48 x 8.43 x 2.64 in)	Warranty	Axis 3-year warranty, see www.axis.com/warranty
Weight	1.4 kg (3.2 lb)	Environmental responsibility: www.axis.com/environmental-responsibility	
Maximum load	30 kg (66 lb)		
Cable routing	Back: Cable hole Bottom: AXIS T91G61 or AXIS T98A required		