

HP DreamColor Z27x Studio Display



Work in brilliant, trusted color and bring your ideas to life with the HP DreamColor Z27x Studio Display, featuring HP's unrivaled integrated calibration engine, 4K¹ input support, and 10-bit color that drives up to 1.07 billion onscreen colors.



Astonishing performance for the color professional

- Consistently deliver rich, accurate colors and ultra-deep blacks with HP's custom-engineered 27-inch diagonal DreamColor panel. Get massive 2560 × 1440 resolution and crisp, clear presentation from 1000:1 typical, 800:1 minimum contrast ratio and high brightness.²

The power tool for your color workflow

- Experience up to 1.07 billion colors with 1,024 tones per channel as the HP DreamColor Engine 2 powers through your 4K content¹ with 10-bit color accuracy and easily handles today's most demanding professional workflows.

Color customization at your fingertips

- Create your own color space with just one-touch with the integrated calibration engine. Enjoy seamless compatibility with a range of professional colorimetric devices, including the optional HP DreamColor Calibration Solution.³

Featuring

- Experience custom-engineered advanced Off-Axis Black technology, second-generation IPS, and digital cinema-class color gamuts.
- Enjoy stunning 10-bit color and 1,024 gray levels per channel—4x greater than standard 8-bit displays—and up to 1.07 B onscreen colors driven by the HP DreamColor Engine 2.
- Get push-button color accuracy out of the box with 7 color space presets or use the integrated calibration engine to create your own.
- Enjoy fast and flexible display calibration and management through two HP DreamColor USB ports.
- Manage and control your fleet of HP Z27x Displays remotely with the integrated Ethernet interface and web server.⁵
- Eliminate distractions and accelerate productivity in low-light environments with the HP Night Vision UI's auto-fade button backlights and four programmable hotkeys.
- Connect your display to a workstation and a range of digital video devices with one HDMI and two DisplayPort inputs and a 4-port USB hub.
- Create a clean, compact all-in-one with the optional HP Thin Client Mount Kit³ and reduce the effects of harsh lighting with the optional HP DreamColor Hood Kit.³
- Be a better consumer with a display that has environmentally responsible components that include low halogen⁶, arsenic-free glass, and mercury-free backlights.
- Rest assured that your IT investment is supported by a three-year standard limited warranty. Select an optional HP Care service⁷ to extend your protection up to 5 years.



HP DreamColor Z27x Studio Display Specifications Table



Product Number	D7R00A4
Display Size (diagonal)	27"
Viewing Angle	178° horizontal; 178° vertical
Brightness	48 to 250 cd/m ² calibrated ¹
Contrast Ratio	800:1 static ¹
Response Time	7 ms gray to gray ¹
Aspect Ratio	16:9
Native Resolution	2560 x 1440
Resolutions Supported	4096 x 2160; 3840 x 2160; 2560 x 1600; 2560 x 1440; 2048 x 1080; 1920 x 1200; 1920 x 1080; 1600 x 1200; 1366 x 768; 1280 x 1024; 1280 x 720; 1024 x 768; 800 x 600; 720 x 576; 720 x 480; 640 x 480
Display Features	Plug and Play; Anti-glare; User programmable; Language selection; On-screen controls; LED Backlights; In plane switching
User Controls	Back; Up (adjusts the settings up); Down (adjusts the settings down); Select; Menu; Power
Input Signal	1 HDMI 1.4 (with HDCP support); 2 DisplayPort 1.2 (with HDCP support);
Ports and Connectors	4 USB 3.0 (two side and two rear); 2 USB 2.0 DreamColor ports; 1 analog and digital audio output
Input Power	Input voltage: 90 to 265 VAC
Power Consumption	< 110 W (maximum), 65 W (typical), ≤ 1.2 W (standby)
Dimensions with Stand (W x D x H)	25.24 x 9.55 x 15.55 in 64.1 x 24.24 x 42.04 cm
Dimensions without Stand (W x D x H)	25.24 x 2.58 x 14.93 in 64.1 x 6.55 x 37.92 cm
Weight	19.4 lb 8.8 kg With stand
Ergonomic Features	Tilt: -5 to +20°; Swivel: ±45°; Pivot rotation: 90°
Environmental	Arsenic-free display glass; Mercury-free display backlights; Low halogen ²
Expandable Solutions	Dreamcolor
What's in the box	Monitor; AC power cord; DisplayPort cable; USB cable; HDMI cable; DisplayPort mini cable; DVD documentation kit; Factory calibration report
Warranty	Protected by HP, including a 3-year standard limited warranty. Optional HP Care Pack Services are extended service contracts that extend your protection beyond the standard warranties. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc . HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

See important legal disclaimers on the last page

Accessories and services (not included)

HP DreamColor Calibration Solution



The HP DreamColor Calibration System (DCS) is an LCD monitor option designed for professional users who require precision color accuracy in their work output. It allows users to quickly and accurately calibrate monitor front-of-screen settings to prevent any drift of critical monitor color or whitepoint settings.

Product number: B1F63AA

HP LCD Speaker Bar



The LCD Speaker Bar seamlessly attaches to the bezel of the HP Business Monitor and provides full multimedia capabilities.

Product number: NQ576AA

HP Thin Client Mount Kit



Attach your HP Thin Client or USDT PC to the back of select HP Z Displays and maintain optimal ergonomic adjustability with the HP Thin Client Mount Kit.¹

Product number: E5J35AA

HP HD141 Hood Kit for Z27x



Customize your HP DreamColor workspace. Create an ideal lighting environment for your HP Z27x DreamColor Display with the HP HD141 Hood Kit for Z27x.

Product number: G0M47AA

Messaging Footnotes

¹ 4K content required to view 4K resolution.

² All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

³ Sold separately.

⁴ Scale to full frame with DCI aperture management or display 1:1 with pan and zoom.

⁵ Internet access required and sold separately.

⁶ External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

⁷ Sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

Technical Specifications Footnotes

¹ All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

² External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

Sign up for updates
hp.com/go/getupdated

Learn more at
hp.com

© Copyright 2014, 2016 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

