



HP EliteDisplay E202 20-inch Monitor

Get comfortable and be productive with the affordable, easy-to-deploy HP EliteDisplay E202 20-inch Monitor, an HD+ IPS display that is Certified for Windows 10 and includes excellent ergonomic adjustability and crisp, clear color presentation.



It's all in the details.

- Show and share projects around the room with 178-degree, wide-angle IPS technology. Keep your work front and center on the ample 20-inch diagonal screen and enjoy 1600 x 900¹ HD+ color and clarity for all of your content.

Find your comfort zone.

- Settle into your most comfortable position with adjustable tilt and swivel settings and an impressive 150 mm height adjustment range. Use pivot rotation to customize portrait or landscape views.

Ports for every peripheral.

- Connect to a range of PCs and devices with HDMI, DisplayPort, and VGA inputs. The integrated USB hub keeps everyday devices close at hand with USB connections at the display.
- Attach your HP Desktop Mini, HP Chromebox, or select HP Thin Client directly behind the display.² Keep things tidy with an integrated power supply and cable management features.
- Connect the display to your PC or notebook and experience all Windows 10 has to offer.
- Get an intelligent, energy-efficient design that is ENERGY STAR[®] certified, EPEAT[®] Gold registered³, and meets TCO Certified Edge requirements with 85% Post-Consumer Recycled plastics.
- Design the screen for how you work with HP Display Assistant software.
- Customize a complete solution with HP accessories.⁴ Add audio with the HP Speaker Bar, use an HP Single Arm to take the display off the desk, or choose an HP USB Graphics Adapter for multi-monitor⁵ setups.
- Get three years of service and support, and extend your protection with optional HP Care Packs.⁵



Ergonomic Display



Displayport,
HDMI, VGA



Efficient Workspace

HP EliteDisplay E202 20-inch Monitor Specifications Table



Product Number	M1F41AA
Display Size (diagonal)	50.8 cm (20")
Display Type	IPS w/LED backlight
Panel Active Area	17.43 x 9.81 in; 442.8 x 249.075 mm
Viewing Angle	178° horizontal; 160° vertical
Brightness	250 cd/m ² ¹
Contrast Ratio	1000:1 static; 5000000:1 dynamic ¹
Response Time	7 ms gray to gray ¹
Aspect Ratio	16:9
Native Resolution	1600 x 900 @ 60 Hz (The video card of the connected PC must be capable of supporting 1280 x 720 at 60 Hz and include 1 HDMI outputs to drive the monitor at the Preferred Mode.)
Resolutions Supported	1600 x 900; 1440 x 900; 1280 x 1024; 1280 x 800; 1280 x 720; 1024 x 768; 800 x 600; 720 x 400; 640 x 480
Display Features	Anti-glare; In plane switching; Language selection; LED Backlights; On-screen controls; Pivot rotation; Plug and Play; User programmable
User Controls	Menu; Minus ("-")/Information; Plus ("+") /Input Control; OK/Auto; Power
Input Signal	1 VGA; 1 HDMI (with HDCP support); 1 DisplayPort 1.2 (with HDCP support);
Ports and Connectors	3 USB 2.0 (two downstream and one upstream) ¹
Input Power	Input voltage: 100 to 240 VAC
Power Consumption	33 W (maximum), 22 W (typical), 0.5 W (standby)
Dimensions with Stand (W x D x H)	18.85 x 7.44 x 19.42 in 47.9 x 18.9 x 49.33 cm
Dimensions without Stand (W x D x H)	18.85 x 7.44 x 11.68 in 47.89 x 4.97 x 29.67cm Without stand
Weight	10.12 lb 4.6 kg With stand
Ergonomic Features	Tilt: -5 to +20°; Swivel: ±45°; Height: 150 mm; Pivot rotation: 90°
Environmental	Arsenic-free display glass; Mercury-free display backlights; Low halogen ²
What's in the box	Monitor; AC power cord; USB cable; DisplayPort cable; VGA cable; CD (includes User Guide, warranty, drivers)

See important legal disclaimers on the last page

Accessories and services (not included)

HP PC Mounting Bracket for Monitors



Customize an altogether better solution with the HP PC Mounting Bracket for Monitors, which lets you attach your HP Desktop Mini, HP Chromebox, or select HP Thin Client directly behind select HP Z Displays and EliteDisplays.
Product number: N6N00AA

HP Desktop Mini Security/Dual VESA Sleeve



Wrap your HP Desktop Mini PC in the HP Desktop Mini Security/Dual VESA Sleeve to securely mount your PC behind your display, position your solution on a wall, and lock it down with the optional HP Ultra-Slim Cable Lock.
Product number: G1K22AA

HP Single Monitor Arm



The HP Single Monitor Arm is the perfect desk accessory for your work life. Sleek and streamlined, the HP Single Monitor Arm is designed to complement the way you work.
Product number: BT861AA

HP Adjustable Dual Display Stand



The HP Adjustable Dual Display Stand allows you to use two displays to maximize your productivity and optimize efficiency. Either or both displays can be rotated to landscape or portrait orientation, and the stand is depth-, height-, tilt-, and angle-adjustable so you can view both screens at eye-level as well as slightly facing each other, letting you track multiple applications and information sources at the same time. Integrated base rollers let you rotate the stand so you can more easily share your work.
Product number: AW664AA

HP LCD Speaker Bar



The LCD Speaker Bar seamlessly attaches to the bezel of the HP Business Monitor and provides full multimedia capabilities.
Product number: NQ576AA

HP UHD USB Graphics Adapter



Boost your productivity by extending or mirroring your desktop to a UHD display with the HP UHD USB Graphics Adapter.
Product number: N2U81AA

HP 4 year Next business day Exchange Standard Monitor Service



HP Hardware Support Exchange Service offers a reliable and fast exchange service for eligible HP products. Specifically targeted at products that can easily be shipped and on which customers may easily restore data from backup files, HP Hardware Support Exchange Service is a cost-efficient but still convenient alternative to onsite support. HP Hardware Support Exchange Service provides a replacement product or part to be delivered free of freight charges to your location within a specified period of time. Replacement products or parts are new or equivalent to new in performance.
Product number: U0J10E

Messaging Footnotes

¹ All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

² Requires HP PC Mounting Bracket for Monitors, sold separately. See product QuickSpecs for exact PC and thin client compatibility.

³ EPEAT® registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.

⁴ Each sold separately.

⁵ Sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

Technical Specifications Footnotes

¹ All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

² External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

Sign up for updates
hp.com/go/getupdated

Learn more at
hp.com

The product could differ from the images shown. © 2015 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. Specific features may vary from model to model. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR® and the ENERGY STAR® mark are registered trademarks of the U.S. Environmental Protection Agency.

