



HP ProDisplay P19A 19-inch LED Backlit Monitor

Essential business functionality in a 5:4 aspect ratio monitor designed for the way you work and the tools you use every day.



Get solid performance in a stylish display designed with the environment in mind at a very attractive price point.

Boost productivity with essential functionality at an affordable price

Increase optimal viewing and easy readability of software and tools designed for 5:4 aspect ratio presentations – ideal in banking, healthcare, financial, POS, retail and other business environments.

Get vibrant text and graphics from the LED backlit panel. LED technology also makes the monitor thin, light, and easy to position on the desk. High contrast ratios and fast response times keep your content crisp and readable throughout the day.¹

The 19-inch diagonal screen offers ample workspace for multiple applications while the compact, 5:4 aspect ratio has a smaller footprint and saves space on the desk. Work comfortably throughout the day with up to 30 degrees of tilt on the adjustable design. Minimize clutter on the desktop and enjoy a simplified setup and deployment with the internal power supply.

Get compatible with HP accessories

Free up valuable desk space by mounting on a wall utilizing the 100-mm standard VESA pattern which supports the HP Quick Release (sold separately)².

Customize your work space with accessories like the HP Integrated Work Center Stand and HP Speaker Bar (sold separately)².

Get peace of mind

Stable product lifecycle and minimum one-year lifespan help ensure product consistency across staggered deployments. HP quality standard testing that puts our monitors through their paces before you do. Rest assured that your IT investment is supported by a three-year standard limited warranty. Select optional HP Care Pack Services³ to extend your protection beyond the standard warranties.

Earn your environmental stripes

Mercury-free LED display backlighting, a low halogen⁴ design and arsenic-free⁵ display glass are just a few of the display's responsible details. Lower your overall bottom line with award-winning eco-certifications, including ENERGY STAR®, EPEAT® Gold⁶, and TCO.

HP ProDisplay P19A 19-inch LED Backlit Monitor

Part number	D2W67AA
Panel type	TN with LED backlight
Viewable image area	48,26 cm (19 in) diagonally measured
Viewing angle	Horizontal: 170 degrees; Vertical: 160 degrees
Brightness¹	250 nits (cd/m ²)
Contrast ratio¹	Static: 1000:1; Dynamic: 1,000,000:1
Response rate¹	5 ms (on/off)
Frequency	Horizontal: 30 KHz-83 KHz; Vertical: 50 Hz-76 Hz
Aspect ratio	5:4
Native resolution	1280 x 1024 @ 60 Hz
Resolutions supported	640 x 480 @ 60 Hz, 720 x 400 @ 70 Hz, 800 x 600 @ 60 Hz, 1024 x 768 @ 60 Hz, 1280 x 960 @ 60 Hz, 1280 x 1024 @ 60 Hz
Input signal	VGA
User controls	OK/Menu, Auto/Minus, Plus, Power
Power consumption	Maximum: 25 W; Typical: 15 W; Power saving: 0.5 W
Dimensions (w x d x h)	Unpacked: 41,4 x 20,64 x 41,82 cm (16.3 x 8.13 x 16.46 in) Head only: 41,4 x 5,82 x 34,7 cm (16.3 x 2.3 x 13.7 in)
Weight	Unpacked: 3,47 kg (7.65 lb); Head only: 2,99 kg (6.59 lb); Packaged: 4,5 kg (9.92 lb)
Base features	Tilt: -5 degrees to +25 degrees
Environmental	Operating: 5° to 35° C (41° to 95° F); Non-operating: -20° to 60° C (-34° to 140° F)
Accessories² (sold separately)	HP Integrated Work Center Stand - USDT and Thin Clients) - Allows mounting of a 17 - 24 inch diagonal HP LCD monitor and an HP Ultra-slim Desktop PC as well as select HP Thin Clients on a single stand for the convenience of an "all-in-one" form factor. Part number LH526AA. HP LCD Speaker Bar - Optional; powered directly by the connected PC, seamlessly attaches to the monitor's bezel to bring full multimedia support to select HP LCD monitors; features dual speakers with full sound range and two external jacks for headphones. Part number NQ576AA. HP USB Graphics Adapter - Optional; enables connection of up to six simultaneous displays. Use one Adapter to bridge between a notebook or desktop PC and second monitor or use multiple Adapters to connect several displays to each other. Part number NL571AA. HP Business PC Security Lock Kit - Optional; Attaches to the rear of the PC with a six-foot steel cable that can be used to secure a PC or peripherals such as mice, keyboards, monitors or USB security devices to protect them against unauthorized removal by physically connecting the system to an anchor point. Part number PV606AA. HP LCD Monitor Quick Release⁷ - An easy-to-use, VESA-compliant, LCD monitor mounting solution that allows you to quickly and securely attach an LCD monitor to a variety of stands, brackets, arms or wall mounts. Part number EM870AA.
Certification and compliance	CB, CE, TCO, CCC, CEL 1, CECP, BSMI, S-Mark, VCCI, FCC, CSA, GS mark, ICES, C-Tick, e-Standby, ENERGY STAR® qualified, EPEAT® Gold ⁵ (select regions)
Limited warranty	Protected by HP, including a 3 year standard limited warranty. Optional HP Care Pack Services ³ are extended service contracts that extend your protection beyond the standard warranties.

1. All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

2. Each accessory and mounting hardware is sold separately.

3. Service levels and response times for HP Care Pack Services may vary depending on your geographic location. Service starts from date of hardware purchase. Restrictions and limitations apply. HP Care Pack Services extend service contracts beyond the standard warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at www.hp.com/go/lookuptool. Additional HP Care Pack Services information by product is available at www.hp.com/hps/carepack.

4. External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

5. Arsenic and its compounds were not detected using U.S. EPA test methods 3052/6010b by ICP-AES with a MDL 10 ppm.

6. EPEAT® Gold registered models of this product are available where HP registers commercial display products. See www.epeat.net for registration status in your country.

7. The HP Quick Release has been designed to support a maximum of up to 24 lbs (10.9 kg) for all devices mounted. Because mounting surfaces vary widely and the final mounting method and configuration may vary, mounting fasteners are not supplied (other than the VESA-compliant screws). HP recommends that you consult with a qualified engineering, architectural or construction professional to determine the appropriate type and quantity of mounting fasteners required for your application and to ensure that your mounting solution is properly installed to support applied loads.

© Copyright 2013 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR is a registered mark owned by the U.S. government. February 2013

