



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

273-TB

UPC Number:

78621000273

Status:

Active

Description:

Squeeze Connector, 90 Degree Bend, Trade Size 1 Inch, Knockout Size 1 Inch, Cable Range 1.187 to 1.406 Inch, Malleable Iron

Features

Cap lifts off by simply loosening screws part way, only two screws to tighten.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)	1
Material	Malleable Iron
Finish	Zinc Plate

Dimension Information

Dimension A (inches)	2 3/8
Dimension B (inches)	2 7/32
Dimension C (inches)	2 7/16
Knockout Size (inches)	1
Cable Opening-Minimum (inches)	1.187
Cable Opening-Maximum (inches)	1.406

Packaging

T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	62.81 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com