

**Armored Cable/Flexible Metal Conduit Fittings****T&B Catalog Number:**

331

UPC Number:

78621000331

Status:

Active

Description:

3 Inch. Tite-Bite 90 Degree Connector, Malleable Iron-Electro Zinc Plated.

Features

The angle clip gives secure mechanical grip that tightens under tension or vibration

Throat is long enough to install in cast housing knockouts.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)

3

Material

Malleable Iron

Finish

Electro Zinc Plated

Dimension Information

Dimension A (inches)

5 25/32

Dimension B (inches)

7

Knockout Size (inches)

3

Cable Opening-Minimum (inches)

3.312

Cable Opening-Maximum (inches)

3.562

Specifications

3dmodel

Available on Website

Packaging

Package in Units

1

T&B Sold in UOM

Each

T&B Weight Per UOM

7.8 lbs. per 100

Notes

U.L. Listed for flexible metal conduit only.

Certifications

RoHS Compliance

No

Certifications

File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com