

**Armored Cable/Flexible Metal Conduit Fittings****T&B Catalog Number:**

3312-TB

UPC Number:

78621003312

Status:

Active

Description:

1/2 Inch, Two Screw Connector, Steel, 1/2 Inch Knockout, CSA Certified for Aluminum, Grounding Type, For Sheathed Cable 2 #8, 3 #8 4 #10, Cable Opening .813 Inch to .938 Inch

Features

Formed steel body with carefully round bushing.

The armor gripping saddle stays open by itself when cable is being inserted.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)	1/2
Material	Steel

Dimension Information

Dimension A (inches)	1 3/32
Dimension B (inches)	1 5/8
Dimension C (inches)	1 3/8
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.500
Cable Opening-Maximum (inches)	0.937

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	50
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	102 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-001571
--------------------	------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications

File Nbr:

E 1383

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com