Thomas&Betts





Standard Barrel Copper Lug
T&B Catalog Number:

54104I

UPC Number: 78620993630
Status: Active
Description:

Copper One-Hole Insulated Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size #8 AWG, #10 Bolt Size, Tin Plated, Die Code 21, Die Color Code Red

Features

	Translucent nylon insulator provides easy viewing of die code/color.
	Variety of options available - finish, tongue width and angle, bolt hole size/ spacing and more.
	Easy to install with standard Color-Keyed compression tools.

General

Insulation Type	Nylon
Material	Copper
Finish	Tin Plated
Wire Size	#8 AWG
Number of Studs	1
Stud Size	#10
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Red
Die Code	21

Dimension Information

A (inches)	1.49
B (inches)	0.5
C (inches)	0.39
D (inches)	0.08
E (inches)	0.35

Specifications

Temperature Rating	105°C
Voltage Rating	600V

Tooling

Connector & Tooling Chart	Available on Website

Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	11.25 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000451
Overview	Available on Website

Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications

RoHS Compliance	Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com