

Narrow-Tongue Copper Lug

T&B Catalog Number:

54152NT

UPC Number:

78620986791

Status:

Active

Description:

Copper One-Hole Lug, Standard Barrel Narrow Tongue, Peep Hole, Max 35kV, Wire Size 1/0 AWG, 1/4 Inch Bolt Size, Tin Plated, Die Code 42, Die Color Code Pink

General

Material	Copper
Finish	Tin Plated
Wire Size	1/0 AWG
Number of Studs	1
Stud Size	1/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Narrow
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Pink
Die Code	42

Dimension Information

A (inches)	1.600
B (inches)	0.650
C (inches)	0.521
D (inches)	0.125
E (inches)	0.521
F (inches)	0.250

Specifications

Voltage Rating	600V
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging


T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	5.88 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000288
T&B Instruction Sheets	ta00675-tb2

Notes

Dimensions given for reference only. Dimensions may vary up to .030.



Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com