



Aluminum Lug T&B Catalog Number:

UPC Number:

ATL20-12

Status:

78378661096

Description:

Active

Type Aluminum One-Hole Lug, Max 35kV, Wire Size 2/0 Str, 1/2 Inch Bolt Hole, Tin Plated, Die Color Olive

Features

Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.

Specifically chamfered barrel for ease of installation.

Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

General

Material	Aluminum
Finish	Tin Plated
Wire Size	2/0 Str.
Number of Studs	1
Stud Size	1/2
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Die Color	Olive

Dimension Information

A (inches)	1 3/16
B (inches)	1 3/8
C (inches)	11/16
L (inches)	3
T (inches)	7/32
W (inches)	1 1/32

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	9 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000516
T&B Instruction Sheets	ta01325-tb2

Notes

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com