



## Aluminum Lug

### T&B Catalog Number:

ATL202

UPC Number:

78378661104

Status:

Active

Description:

Type Aluminum Two-Hole Lug, Max 35kV, Wire Size 2/0 Str, 1/2 Inch Bolt Hole, Tin Plated, Die Color Code Olive

### Features

Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.

Specifically chamfered barrel for ease of installation.

Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

### General

Material	Aluminum
Finish	Tin Plated
Wire Size	2/0 Str.
Number of Studs	2
Stud Size	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Die Color	Olive

### Dimension Information

A (inches)	1 3/16
B (inches)	3 3/8
C (inches)	3/4
L (inches)	5
T (inches)	7/32
W (inches)	31/32

### Specifications

Voltage Rating	35KV
----------------	------

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	14.56 lbs. per 100

### Application Support

T&B Instruction Sheets	ta01325-tb2
------------------------	-------------

### Notes

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:

Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)