



Aluminum Lug

T&B Catalog Number:

ATL2-14

UPC Number:

78378661082

Status:

Active

Description:

Type ATL Aluminum One-Hole Lug, Max 35kV, Wire Size 2 Str, 1/4 Inch Bolt Hole, Tin Plated, Die Color Code Pink

Features

Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.

Specifically chamfered barrel for ease of installation.

Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

General

Material	Aluminum
Finish	Tin Plated
Wire Size	2 Str.
Number of Studs	1
Stud Size	1/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Die Color	Pink

Dimension Information

A (inches)	27/32
B (inches)	25/32
C (inches)	11/32
L (inches)	1 15/16
T (inches)	3/16
W (inches)	23/32

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	3.44 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000516
T&B Instruction Sheets	ta01325-tb2

Notes

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com