



Aluminum Lug T&B Catalog Number:

UPC Number: ATL2502
78378661118
Status: Active
Description:

Type Aluminum Two-Hole Lug, Max 35kV, Wire Size 250 kcmil, 1/2 Inch Bolt Hole, Tin Plated, Die Color Code Red

Features

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.
- UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

General

Material	Aluminum
Finish	Tin Plated
Wire Size	250 kcmil
Number of Studs	2
Stud Size	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Die Color	Red

Dimension Information

A (inches)	2 1/32
B (inches)	3
C (inches)	1/2
L (inches)	5 25/32
T (inches)	1/4
W (inches)	1 9/32

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	20 lbs. per 100

Application Support

T&B Instruction Sheets	ta01325-tb2
------------------------	-------------

Notes

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com