



Ferrule

T&B Catalog Number:

F9016

UPC Number:

78621033593

Status:

Active

Description:

Non-Insulated Ferrule, Length .472 Inches/12mm, Inner Diameter .110 Inches/2.8mm, Outer Diameter .158 Inches/4mm, Conductor Size 12 AWG/4mm, Copper, Tin Plated

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.

General

Ferrule Type	Uninsulated
Insulation Type	Non-Insulated
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	12
Wire Size (mm ²)	4.00

Dimension Information

A (mm)	12.0
Diameter C (inches)	.110
Diameter C (mm)	2.8
Diameter D (inches)	.158
Diameter D (mm)	4.0
E (mm)	.20
A (inches)	.472
E (inches)	.008

Specifications

Temperature Rating	150°C
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	T3, ERG4
Recommended Tool	T3, ERG4

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000319
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.



Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com