



Ferrule
T&B Catalog Number:

F9026
 78621033604
 Active

UPC Number:
Status:
Description:

Non-Insulated Ferrule, Length .591 Inches/15mm, Inner Diameter .228 Inches/5.8mm, Outer Diameter .295 Inches/7.5mm, Conductor Size 6 AWG/16mm, Copper, Tin Plated

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



General

Ferrule Type	Uninsulated
Insulation Type	Non-Insulated
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	6
Wire Size (mm ²)	16.00

Dimension Information

A (mm)	15.0
Diameter C (inches)	.228
Diameter C (mm)	5.8
Diameter D (inches)	.295
Diameter D (mm)	7.5
E (mm)	.20
A (inches)	.591
E (inches)	.008

Specifications

Temperature Rating	150°C
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	T3, ERG4
Recommended Tool	ERG4

Packaging

T&B Order Multiple	250
T&B Inner Pack	250
Package in Units	2500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000319
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com