



Splice Connector

T&B Catalog Number:

UPC Number:

Status:

Description:

GG2

78621081259

Active

Non-Insulated Butt Splice, Length 1.72 Inches, Width .55 Inches, Wire Range #2-#1 AWG, Copper, Tin Plated, 25 Pack

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Insulation Type	Non-Insulated
Terminal Series	GG
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	2-1

Dimension Information

Stock Thickness	.05
A (inches)	1.72
B (inches)	.55

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT115A, TBM6, TBM6S
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	250
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	4.25 lbs. per 100
Alternate Package Qty	2G21

Application Support

T&B Sales Drawings	wsd-001494
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Splice not available with cut-out section.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com