



## Ring Terminal T&B Catalog Number:

KV14-10R-M

**UPC Number:**

78621010068

**Status:**

Active

**Description:**

Vinyl Insulated Ring Terminal, Length .898 Inches, Width .335 Inches, Bolt Hole #10, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated

### Features

Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.

### Standards

UL, cULus

### General

Insulation Type	Insulated Vinyl
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Stud Size	#10

### Dimension Information

d1 (inches)	.091
D (inches)	.177
E (inches)	.433
F (inches)	.307
L (inches)	.898
T (inches)	.031
W (inches)	.335

### Specifications

Temperature Rating	75°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Application Tools	WT112M, CM2000A
-------------------	-----------------

### Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	20000
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)