



## Metric Lugs and Splices

### T&B Catalog Number:

**UPC Number:**

MCC70M14

**Status:**

78621096264

**Description:**

Active

Copper One-Hole Metric Lug, Standard Barrel, Peep Hole, Max 35kV, 70mm Wire Size, 14mm Bolt Size, Tin Plated

### Features

Manufactured from seamless copper tubing that conforms to BS2781 with heavy-duty wall thickness, achieving maximum conductivity with low resistance.

Electro Tin-Plated for Corrosion Resistance. Chamfered Barrels Provide Ease of Strand Entry and Inspection hole facilitates full insertion of the conductor.

Cable Area Clearly Identified on Lug.

### General

Style	Metric Standard Barrel Copper Lug
Material	Copper
Finish	Tin Plated
Wire Size	70mm
Number of Studs	1
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round

### Dimension Information

A (mm)	59.0
B (mm)	16.0
C (mm)	25.0
D (mm)	11.3
F (mm)	14.0

### Specifications

Temperature Rating	105°C
Voltage Rating	600V

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	7.19 lbs. per 100

### Application Support

T&B Sales Drawings	wsd-000151
Overview	Available on Website

## Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

## Certifications

RoHS Compliance	Yes
Webcat CE_recognized	Y

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)