



Disconnects

T&B Catalog Number:

THS14-250FD-D

UPC Number:

72849414268

Status:

Active

Description:

Heat-Shrinkable Female - 250 Series Disconnects for Wire Range 12-10 , Yellow

Features

Internal Barrel Serrations. Funnel Entry.

General

Disconnect Type	Female - 250 Series
Insulation Type	Heat-Shrinkable Polyethylene
Material	Brass with Copper Sleeve
Color	Blue
Wire Range	16-14
Tab Size	.260 x .032

Dimension Information

D (inches)	.240
L (inches)	1.340
W (inches)	.260

Specifications

Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-2

Tooling

Application Tools	CM2000A
-------------------	---------

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000377
--------------------	------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com