



## Butt Splice T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

TV14-TV18-L  
72849414201  
Active

Insulated Vinyl Step-Down Butt Splice for Wire Range 16-14 to 22-16,  
Blue with Red Color Ring

### Features

Tubular copper construction prevents barrel separation during crimping and provides good conductivity. Chamfered barrel enables easy funneling of copper strands into splice barrel. Expanded entry accommodates larger/thicker wiring insulation. Color-coded insulator ring make it easy to identify the wire size capacity of each end of the splice.

### General

Insulation Type	Insulated Vinyl
Material	Copper
Finish	Tin-plated
Color	Blue
Wire Range	16-14

### Dimension Information

D (inches)	0.18
L (inches)	0.97

### Specifications

Temperature Rating	75°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Application Tools	CM2000A
-------------------	---------

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 1000
Alternate Package Qty	TV14TV18M

### Application Support

T&B Sales Drawings	wsd-000279
--------------------	------------

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)