



Low Smoke T&B Catalog Number:

UPC Number:

Status:

Description:

TYV25M

78621059509

Active

Fluoropolymer Cable Tie, Maroon Fluoropolymer ECTFE, for up to 150 Degrees Celsius (302 F) for Applications Where Smoke Generation is a Concern, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.17mm (0.02Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

General

Material	Fluoropolymer
Color	Maroon

Dimension Information

Nominal Length (inches)	7
Length (inches)	7.31
Width (inches)	.184
Max. Wire Bundle Diameter (inches)	1.75

Specifications

Temperature Rating	-50°F to 284°F
Flammability Rating	UL 94 V-0

Tooling

Application Tools	ERG50, WT1-TB
-------------------	---------------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	4.38 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com