

FGS-KTW2-R | 1438999

FiberGuide® Vertical Duct Kit, slotted hinged cover, 2 in x 4 in, 6 ft length, 2" slot spacing

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	100 mm x 50 mm 4 in x 2 in
Length	1829.0 mm 6.0 ft

Environmental Specifications

Flammability Rating	UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel LSZH TCO '99 WEEE
Safety Standard	UL

General Specifications

Product Type	Slotted channel with hinged cover
Brand	FiberGuide®
Color	Yellow
Section Type	Vertical section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant