



Liquidtight Flexible Metal Conduit Fittings

T&B Catalog Number:

UPC Number:

5247GR

Status:

78621089615

Description:

Active

2 Inch 45 Degree Malleable Iron External Bonding Liquidtight Connector,
Non-insulated

Features

Ability to install quickly with low torque effort

Application

To positively bond conduit to box or enclosure

General

Trade Size (inches)	2
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating
Ground Wire	4-2/0

Dimension Information

Dimension A (inches)	3 13/16
Dimension B (inches)	3 7/8
Dimension C (inches)	7/8

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	2.56 lbs. Each

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:

E 3060

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com