

**Liquidtight Flexible Metal Conduit Fittings****T&B Catalog Number:**

5359GR

UPC Number:

78621089638

Status:

Active

Description:

3 Inch 90 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

Features

Ability to install quickly with low torque effort

Application

To positively bond conduit to box or enclosure

General

Trade Size (inches)	3
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating
Ground Wire	2-4/0

Dimension Information

Dimension A (inches)	5 3/16
Dimension B (inches)	10 1/4
Dimension C (inches)	1

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	14.25 lbs. Each

Certifications

RoHS Compliance	No
-----------------	----

Certifications

File Nbr:

E 3060

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com