



Flexible Conduits & Fittings

T&B Catalog Number:

BVIDB-U237GT

UPC Number:

78620994975

Status:

Active

Description:

PMAFIX black female thread adapter with UNEF threads and universal safety clip. Material - polyamide 6, thread size - 15/16 in. - 20, nominal width/conduit size - 17.

Application

For cable protection systems in a wide range of applications

Characteristics

Very high impact resistance
Vibration proof connection to PMAFLEX conduits
Easy installation, simply push the conduit in
High conduit pull-out strength
Can be easily re-opened with a screwdriver
Very good chemical properties
Free from halogens and cadmium
Fits both conduit profiles - fine (T) and coarse (G)

General

Material: Polyamide 6
Color: Black
Thread Type: UNEF
Compatible With: PMAFLEX/ Souriau connector series UTG-6 / ITT Cannon Trident

Dimension Information

Fits to Conduit Size (NW): 17
Fits to Conduit Size (metric): 20
Fits to Conduit Size (inches): 1/2
Thread Size (UNEF): 15/16" - 20

Technical Information

Temperature Range-Continuous (Celsius): -40 degree C to +105 degree C
Temperature-Short-Term (Celsius): +160 degree C
Technical Data Sheet: Available on Website
Chemical Resistance Chart: Available on Website

Specifications

3dmodel: Available on Website

IP Ratings

IP Rating: IP 68 stat. / IP 54 dyn. On conduit side

Packaging

T&B Order Multiple: 50
T&B Inner Pack: 50
Package in Units: 800
T&B Sold in UOM: Each
T&B Weight Per UOM: 0.02 lbs. Each

Application Support

PMA Reference Guide: Available on Website

Product Overview-PMAFIX Connectors Available on Website
PMAFIX Connectors-Safety and Sealing Systems Available on Website

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com