

Two-Piece - Outer sleeve

T&B Catalog Number:

GSC405

UPC Number:

78621081402

Status:

Active

Description:

Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .405 Inches/10.28mm, Outer Diameter .453 Inches/11.50mm, Color Red, Soft Bronze, Tin Plated



Features

Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Outer sleeve for the Hexagonal Range (the outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.



General

Material	Soft bronze
Finish	Tin plated (per MIL-T-10727A)
Color	Red

Dimension Information

Length (inches)	.252
Length (mm)	6.4
Inner Diameter (inches)	.405
Inner Diameter (mm)	10.28
Outer Diameter (inches)	.453
Outer Diameter (mm)	11.5

Tooling

Installation Tools	11901A, WT540
--------------------	---------------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000206
Overview	Available on Website
Installation Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

