

# 1U Rack-Mount Console with 19-in. LCD

MODEL NUMBER: **B021-000-17**



## Description

Tripp Lite's B021-000-17 1U Rackmount Console features an integrated 19" LCD panel, full 88-key keyboard, and touch pad, all in a 1U rackmountable housing. The included KVM cable kit allows for connection to a PS/2 computer or KVM, and a PS/2 to USB adapter is included, which can be used to connect to a USB computer or KVM. The unit features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.. Your peripheral device connects to the USB type A port on the front of the unit, and your computer connects to the USB type A port on the back of the unit using a Tripp Lite UR020-Series type A M/M cable. Constructed of heavy-duty steel housing. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Features

- Space savings with 1U 19-inch, rack-mount drawer design
- Features 19-inch LCD TFT active-matrix, color panel
- Features a USB pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Supports resolutions of up to 1366 x 768
- Included PS/2 to USB adapter allows for connection to a USB computer or KVM
- Sleep mode when the monitor cover is closed
- Input 120/240 VAC
- Constructed of heavy-duty steel housing
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Highlights

- Control an entire network in just 1U of rack space; includes keyboard, 19" LCD screen, and touch pad
- Features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Connects to a PS/2 or USB server or KVM switch
- Supports video resolutions up to 1366 x 768
- Rackmountable in 19-inch system rack (1U), from 27" to 42" deep
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## System Requirements

- Computer or KVM with a VGA monitor port and USB or PS/2 keyboard/mouse ports

## Package Includes

- 1- B021-000-17 1U Rackmount Console
- 1- KVM Cable Kit ( HD15M to HD15M + 2 PS/2 Male )
- 1-PS/2 to USB Adapter
- 1- C13 to 5-15P Power Cord
- 1- User Manual

# Specifications

OVERVIEW	
Users	1



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC; 127V AC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Electrical Consumption	(Line Mode) 30W / (Standby Mode) 5W
Input Frequency	50/60Hz
Input Current	120V (1.2A) / 230V (0.7A)
<b>PHYSICAL</b>	
Color	Black
<b>ENVIRONMENTAL</b>	
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.06 BTU/Hr
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	0
PC/Server Connections	VGA; USB; PS/2
<b>SPECIAL FEATURES</b>	
Cat5 KVM Switch	No
<b>CERTIFICATIONS</b>	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1.
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>