



## Cross Tap Clamps/DeadEnd Clamps

### T&B Catalog Number:

**UPC Number:**

XT34

**Status:**

78378640036

**Description:**

Active

Copper Type XT - Clamp for Tee-Tap, Cross, Parallel and End-to-End for Wire Range Main: 500 - 1000 kcmil Tap: 500 - 1000 kcmil, Bolt Size 7/16

### Features

Castings of copper alloy. Bolts of silicon bronze.

Designed to enable free wrench rotation for faster installation.

### General

**Style** Type XT - Clamp for Tee-Tap, Cross, Parallel and End-to-End

**Material** Copper

**Conductor Range AWG Main** 500 - 1000 kcmil

**Conductor Range AWG Tap** 500 - 1000 kcmil

### Dimension Information

**Bolt Size (inches)** 7/16

**H (inches)** 3 1/8

**L (inches)** 2 11/36

**W (inches)** 2 11/16

**Conductor Diameter A** .811 - 1.152

**Conductor Diameter B** .811 - 1.152

### Packaging

**T&B Order Multiple** 10

**Package in Units** 10

**T&B Sold in UOM** Each

**T&B Weight Per UOM** 240 lbs. per 100

### Notes

To order tin-plated style, add suffix P (e.g. XT12P)

4 bolt clamps

### Certifications

**RoHS Compliance**

Yes

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com