



Two-Bolt Connector

T&B Catalog Number:

UPC Number:
Status:
Description:

2B20X
78378640009
Active

Copper Type 2BX - One piece Two-Bolt Connector without spacer for Wire Range Main: 2 - 2/0 Str. Tap: 8 Sol. - 2/0 Str. , Bolt Size 1/2

Features

Single-piece construction. Castings and bolts of high-strength copper alloy. Neoprene washer holds free bolt in place during installation.

UL 486A listed for copper conductor only.

General

Style	Type 2BX - One piece Two-Bolt Connector without spacer
Material	Copper
Conductor Range AWG Main	2 - 2/0 Str.
Conductor Range AWG Tap	8 Sol. - 2/0 Str.

Dimension Information

Bolt Size (inches)	1/2
D (inches)	5/16
H (inches)	1 1/2
L (inches)	1 5/16
Conductor Diameter B	.420 - .838

Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	20.81 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com