

Plain Edge Cable Clamps

T&B Catalog Number:

N6NY-009-0-C

UPC Number:

72849410074

Status:

Active

Description:

Plain Edge Cable Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 12.7mm (0.50 Inches), Thickness of 1.52mm (0.06 Inches), Hole Diameter of 5.16mm (0.203 Inches), #10 Screw Mounting with Closed Diameter of 14.27mm (0.562 Inches), 100 Pack

Features

Fully radiused inside edges with size markings in inches and millimeters for easy identification.

Plain edge cable clamps are designed to perform to NAS-1397P.

General

Material	Nylon 6/6
Color	Black
Mounting Method	#10 Screw

Dimension Information

Width (inches)	0.500
Hole Diameter (inches)	0.203
Closed Diameter (inches)	0.562
Max. Wire Bundle Diameter (inches)	0.562
Thickness (inches)	0.060
E (inches)	0.603
X (inches)	0.218

Specifications

Temperature Rating	-40°F to 185°F
--------------------	----------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000525
--------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com

