

**Releasable  
T&B Catalog Number:**

L-10-50R-3-D

**UPC Number:**

72849413081

**Status:**

Active

**Description:**

Releasable Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 280.84mm (11.057 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.31mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

**General**

Material	Nylon 6.6
Color	Orange

**Dimension Information**

Nominal Length (inches)	11
Length (inches)	11.75
Width (inches)	0.298
Max. Wire Bundle Diameter (inches)	3
Min. Wire Bundle Diameter (inches)	1/8

**Specifications**

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

**Tooling**

Application Tools	ERG50, ERG120, QC-100, L-200, L-400-C
-------------------	---------------------------------------

**Packaging**

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	5.63 lbs. per 1000

**Application Support**

T&B Sales Drawings	wsd-000311
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

**Certifications**

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com