



Russellstoll

MaxGard Interconnection Systems

T&B Catalog Number:

DFRF35160

UPC Number:

70891730405

Status:

Active

Description:

MaxGard Fused Male Plug Disconnect Interlocked Receptacle (Nema 12/3R), 30 Amp, 4 Pole 5 Wire, 30Y 120/208V, 60Hz

Features

There are three external lockout points, a door safety switch and a clear shield for test probes.

A fully interlocked MaxGard receptacle

Center ground contacts: make FIRST, break LAST

Application

For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

For use in applications where outdoor, severe or high abuse environments exist.

For use in job site power: for telephone power and communications equipment; portable power connections; portable generator sets; and industrial and shipyard welding.

For use in industrial and commercial applications such as: facilities' electrical power, construction sites, computer-related equipment, welding installations, machiner and entertainment (lighting and sound systems).

General

Style	Load Breaking Fused Male Plug Disconnect Interlock Receptacle
Material	Heavy .060 steel galvanneel with baked enamel, NE-MA 3R/12 Construction
Material_1	Standard 600 V cartridge Fuse Clips and Spacing
Material_2	Pin and sleeves are made from CDA 360 and Marine-grade CDA 485 brass (200a nd 400 amp lines are silver-plated as well).
Frequency	60 Hz
Amperage	30 Amp
Pole/Wire	4P/5W
System	Heavy Industrial & Marine

Dimension Information

Overall Dimensions	Available on Website
--------------------	----------------------

Specifications

NEMA Rating	12/3R
Voltage	3 PhaseY 120/208 Volts AC
Engineering Specifications	Available on Website

Packaging

Package in Units	1
------------------	---

T&B Sold in UOM	Each
T&B Weight Per UOM	35 lbs. Each

Application Support

Overview	Available on Website
Russellstoll Application Guide	Available on Website

Certifications

RoHS Compliance	No
USCG Approved	Y

Certifications



File Nbr:
E5239

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com