

TBM8-750BSCR

Color-Keyed®

12-Ton dieless battery-powered compression tool



General

T&B Instruction Sheets: TA02483-TB2 TA02484-TB2
Type: Manual and Power-Assisted Compression Tools
Application: Up to 900 kcmil copper lugs & splices, Up to 750 kcmil aluminum lugs & splices
T&B UPC: 78621086550
T&B Status: M
Tools specifications: Range Taking Smart tool (Connector Diameter Sensing) crimping #8 AWG through 750 kcmil copper and aluminum connectors. The only additional die sets required are for H-and C-type compression taps: - TBM8-750CL die for C-taps 54755 to 54775 - TBM8-750HG die for H-taps 63110 to 63118 and 63125 - TBM8-750HB die for H-taps 63140 to 63148 - TBM8-750G gauge for tool calibration. Open forged steel head rotates 1800. Rated for 10,000 PSI. Includes carrying case, charger, two batteries and carry strap.
Crimp Type: Indent
Battery: Ni-MH 14.4 V 3.0 Ah
Special Features: Creates Indent-style crimp

Dimension Information

Output Force: 12-Ton
Height: 8-1/2 in.
Length: 19-1/2 in.
Width: 3-7/8 in.