



Split-Bolt T&B Catalog Number:

350HPS

78378685508

Status:

Active

Description:

Type HPS - Split-Bolt Connector with Spacer, Conductor Range for Equal Main and Tap ACSR 266.8-1/0, Conductor Range for Equal Main and Tap 350 kcmil-1/0 Str, Min Tap with One Max Main 2 Sol, Tin Plated

Features

Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style	Type HPS
Wire Type	Copper, Aluminum, ACSR
Material	Copper Alloy
Plating	Electro Tin-Plated
Color	Metallic
Conductor Range for Equal Main and Tap	350 kcmil-1/0 Str.
Conductor Range Min. Tap with one Max. 2 Sol.	
Main	
Conductor Range For Equal Main and Tap ACSR	266.8-1/0

Dimension Information

A (inches)	1 5/16
B (inches)	0.717
C (inches)	1 21/32
D (inches)	2 11/16

Packaging

T&B Inner Pack	1
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	86.19 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000072
--------------------	------------

Notes

Most connectors are UL and CSA Certified for copper conductor only.

Blackburn Contax recommended when used on aluminum conductor.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications

File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com