



BLACKWIRE® 435

Modern style on-the-go.

So compact and lightweight, you'll hardly know it's there.

Style and comfort

BLACKWIRE® 435

KEY FEATURES



- A** Convertible* headset provides mono or stereo wearing options
- B** Noise-canceling microphone
- C** Call answer/end, mute, volume +/-

INCLUDED ACCESSORIES

- Carrying case for easy storage and portability



RECOMMENDED ACCESSORIES

- Neckband kit for behind-the-head wearing*



* Includes neckband and larger carrying case

MODERN STYLE ON-THE-GO

Meet the first headset designed for Unified Communications that's as discreet as it is professionally sound. Providing a choice of mono or stereo audio options and wearing styles, a durable protective carrying case, and the superior audio quality you've come to expect from Plantronics — the Blackwire 435 has the perfect balance of style, sound, and flexibility.

DISCREET, PORTABLE DESIGN

- Its modular design gives end users a choice of mono or hi-fi stereo audio options and wearing styles
- Low profile design is ideal for video conferencing, PC telephony, and other multimedia applications
- Durable, portable design easily tucks into travel case, ideal for professionals on-the-go

SIMPLICITY AND OUTSTANDING AUDIO QUALITY

- Answer/end/mute controls simplify call management while inline indicator lights show call or mute status
- Noise-canceling microphone reduces background noise
- Wideband delivers heightened speech clarity, providing the best possible PC audio quality
- Dynamic EQ feature optimizes your voice quality when on calls and automatically adjusts the EQ settings when you're listening to music or want high quality sound for multi-media playback
- Enhanced digital signal processing (DSP) provides more natural sounding voice

OPTIMIZED FOR UNIFIED COMMUNICATIONS

Connects to	PC or Mac via USB
Compatible with	Windows® or Mac® OS
Ideal for	Video conferencing, conference calls, one-to-one calls, listening to music, webinar audio, and PC phone usage in office or on-the-road
Audio performance	Dynamic EQ, microphone frequency response 100 Hz–8 kHz optimal for wideband voice telephony (up to 6,800 Hz), hi-fi stereo output from 20 Hz–20 kHz, enhanced digital signal processing (DSP), noise-canceling microphone
Hearing protection	SoundGuard: Acoustic limiting for protection against sounds above 118 dBA
Limited warranty	2 years
Models	C435: UC Standard version built for UC applications and softphones from Avaya®, Cisco®, IBM®, Skype®, and more C435-M: Certified for Skype for Business and Optimized for Microsoft® Lync®

For more information about the Blackwire 435 or other Plantronics products, please visit our website at plantronics.com

GLOBAL CUSTOMER CARE

Backed by Plantronics industry-leading global service and support.
+1-800-544-4660 (US and Canada) +1-831-458-7700 (outside US)