



BLACKWIRE 710/720

Corded reliability meets
wireless Bluetooth flexibility

The premium UC headset to seamlessly manage calls
from your PC or mobile device

Multi-device connectivity

BLACKWIRE 710/720

BLACKWIRE 720
(stereo)

BLACKWIRE 710
(monaural)



- A** Durable, metal headband
- B** Ultra-soft ear cushions fold flat for storage
- C** Lights on the ear pad let colleagues know when you're on a call
- D** Call answer/end, mute, volume +/-
- E** Detachable USB cable

INCLUDED ACCESSORY

- Durable carrying case



For more information about the Blackwire 710/720 or any other Plantronics products, please visit our website at plantronics.com

GLOBAL SERVICE AND SUPPORT

Backed by Plantronics industry-leading global service and support.

Plantronics Ltd, Royal Wootton Bassett, UK,
0800 410014 or +44 (0)1793 842200

CORDED RELIABILITY MEETS WIRELESS FLEXIBILITY

The versatile UC headset that offers high-quality PC audio and seamless Bluetooth® connectivity to mobile phones and tablets. Enjoy unmatched audio quality, industry-first smart sensor technology that automatically answers a call when you put on the headset, and a detachable cable for taking your mobile calls throughout the office.

INNOVATIVE, FLEXIBLE DESIGN

- Simple USB connectivity to your PC and detachable cable to take your mobile calls throughout the office
- Intuitive inline controls to answer/end PC and mobile calls, control volume, and mute
- Inline indicator lights and voice prompts give connection, mute and volume status

INTUITIVE PERFORMANCE

- Smart sensor technology lets you answer a call by simply putting on the headset
- Smart Call Transfer automatically routes audio from the mobile phone to the headset whenever it's put on – and vice versa
- Built-in sensors provide contextual information, creating a long-lasting, adaptable platform

UNMATCHED SOUND CLARITY

- PC wideband audio with noise-cancelling microphones for high-quality PC telephony
- Dynamic EQ automatically adjusts audio settings between voice calls and music
- Digital Signal Processing (DSP) provides natural voice sound
- Integrated A2DP lets you listen to streaming media from your mobile phone or tablet

ADDITIONAL INFORMATION

Connects to	PC via USB, mobile phone or tablet via Bluetooth
Ideal for	Users with extensive PC audio and some mobile phone communications
Compatible with	Windows® or Mac OS
Talk time	Up to 10 hours, up to 10 days standby time, up to 6 hours listening time (A2DP)
Wireless frequency	Bluetooth v3.0 + EDR
Audio performance	Dynamic EQ, microphone frequency response 100 Hz–8kHz optimal for wideband voice telephony (up to 6,800 Hz), hi-fi stereo output from 20 Hz–20 kHz (C720 only), enhanced digital signal processing (DSP), noise-cancelling microphone, A2DP
Hearing protection	SoundGuard: Sound levelling for listening comfort and acoustic limiting for protection against sounds above 118 dBA (PC/mobile) SoundGuard DIGITAL: Anti-startle protection detects and eliminates sudden increase in sound and limits the level to 105 dBA; Time Weighted Average (TWA) measurement prevents average daily sound exposure from exceeding 85 dBA (PC only)
Guarantee	2 years

Model	Description	Part number
C710 (monaural)	UC standard version built for UC applications and softphones from Avaya®, Cisco®, IBM®, Skype® and more*	87505-02
C720 (binaural/stereo)		87506-02
C710-M (monaural)	Certified for Skype for Business and optimized for	87505-01
C720-M (binaural/stereo)	Microsoft® Lync®	87506-01

*Download the latest release of Plantronics Spokes™ software to get one-touch call answer/end with these softphones.

Connect with Plantronics

