

107655185 | M14MMO-262

**MMO Type Flush Mounted Angled Faceplate, four port white**



## General Specifications

Color	White
Mount Type	Flush
Product Type	Flush mount outlet
Total Ports, quantity	4
Application	Has 45 degree angular ports for fiber and copper connectors
Package Quantity	1

## Dimensions

Depth	32.77 mm   1.29 in
Height	144.53 mm   5.69 in
Width	83.31 mm   3.28 in
Weight	0.16 kg   0.35 lb

## Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system