

JIC-7858 - Telecom Diagonal Cutter Pliers - Data Sheet

Tapered nose diagonal cutting pliers with standard bevel knives with .030" and .045" skinning holes, with crusher used for multi-purpose wire work, with two V-shaped stripping notches. The comfortable handles are red plastic dipped. Made of chrome vanadium steel.



SPECIFICATIONS	
Cut Type	Diagonal
Includes	Crusher
Stripping Hole	.030", .045"
Skinning Notch	V-Shaped
Jaw Length	7/8"
Jaw Thickness	3/8"
Jaw Width	3/4"
Material	Chrome Vanadium Steel
Color	Red Handle
Length	6-1/4" (158.75mm)
Weight	0.481 lbs
UPC No.	811490010727