

## RC-600 - Ratcheting Cable Cutter - Data Sheet

Cuts up to 600 mcm stranded copper cable, 750 mcm stranded aluminum cable.  
Maximum capacity is 1 3/4" (45mm) diameter.

### FEATURES:

- Cleanly cut copper or aluminum & multi-conductor cable up to 600 mcm (750 mcm for aluminum)
- Unique design to hold and cut cable quickly, easily with minimum effort
- Spring design to hold cutter in the open position when needed
- Quick release for easy opening
- Large ergonomic handle design

(Not designed for cutting ACSR or steel).



### Specifications

Cut Type	Ratcheting
Conductor Material	Aluminum, Copper
Cable Diameter	600 MCM Copper, 750 MCM Aluminum
Max Capacity	1-3/4" (45mm)
Color	Black & Blue Handle
Length	12" (305mm)
Weight	2.452 lbs
UPC No	811490015067