DTK-DP4P Series

Pan/Tilt/Zoom Camera Surge Protection





DTK-DP4P

DTK-DP4PTPV

Product Features

- Each compact design protects power, video and four data conductors
- 5 Amp, 12/24V circuit protects power feeds to camera, heater, blower, defroster
- Single point ground improves protection and speeds installation
- Multi-stage, SAD technology, hybrid design provides the best possible protection

Applications

- PTZ Analog Cameras with Coax (DTK-DP4P) or Twisted Pair Video (DTK-DP4PTPV) Connections
- HD-CVI, AHD and HD-TVI Cameras

Accessories

 DIN Rail Mounting Kit – Part Number DTK-DRK **DITEK's DTKDP4P Series** protects <u>all</u> the sensitive feeds to critical Pan/Tilt/Zoom cameras, not just the video cable. The DP4P protects 12/24 Volt power conductors, 5 Volt RS-422 data pairs, and video conductors – all in one compact design. With the lowest video let through voltage (and best surge protection) on the market, the DP4P provides ideal surge protection for today's sensitive, sophisticated PTZ cameras.

| Technical Specifications | | | |
|------------------------------------|-------------------------------------|------------------|--|
| Part Number: | DTK-DP4P | DTK-DP4PTPV | |
| Service Voltage (Power/Data): | 12/24V AC/DC (Power), <5VDC (Data) | | |
| Service Voltage (Video): | 2V peak-to-peak | <5V peak-to-peak | |
| Clamping Voltage (Power/Data): | 33VAC, 47VDC (Power), 6.8VDC (Data) | | |
| Clamping Voltage (Video): | 2.8VDC | | |
| Protection Modes (Power/Data): | All Lines to Ground | | |
| Protection Modes (Video): | Center-Shield, Shield-G | | |
| Surge Current Rating (Power/Data): | 2,000 Amps/pair (8/20µs) (Power), | | |
| | 114 Amps/pair (10/1000µs) (Data) | | |
| Surge Current Rating (Video): | Center-Shield: | 114A/pair | |
| | 10,000A | (10/100µs) | |
| | Shield-G: 150A | (Data) | |
| Video Band Pass: | 0Hz – 10MHz | 0Hz – 2GHz | |
| Impedance: | 75Ω | N/A | |

Mechanical Characteristics

| Connection Method (Power/Data): | Screw Terminals (#22 - #14 AWG) | |
|---------------------------------|---------------------------------|----------------------------|
| Connection Method (Video): | BNC | Screw Terminals |
| Housing: | ABS | |
| Operating Temperature: | -40°F – 158°F (-40°C – 70°C) | |
| Dimensions: | 3.86"L x 2.09"W x 1.37"H | 3.86L x 2.09"W x 1.59"H |
| | (98mm x 53mm x 35mm) | (98mm x53mm x 40mm) |
| Weight: | 2.56oz (73g) | |

Quality, Standards & Approval

| Agency Approvals: | UL497B |
|-------------------|---------------------------|
| Warranty: | Ten Year Limited Warranty |

Every precaution has been taken to ensure that this literature is accurate and complete. DITEK Corporation assumes no responsibility and disclaims all liability for damages resulting from the use of this information or for any errors or omissions.

Doc. Number: SPS-100061-001 Rev 11 10/16





